

Wagon Brakes

Wagon Brakes with a black finish and glow-in-the-dark handles are specifically designed for use on stage-set designs, but can be used with other mobile jigs and carts. Wagon Brakes provide secure stabilization of your set designs, the ability to effortlessly rearrange sets in an instant, and safety for your crew with special handles that glow in the dark for at least 8 hours. Glow-in-the-dark handles reduce the worry of trip hazards for stagehands as they work to set the scene.

- Lift your scenery off its movable casters
- Black Zinc Finish with Glow-in-the-Dark
 Handle
- 8+ hours glow-in-the Dark Handle
- Secure scenery in place and prevent movement
- Makes lifting easy—with a rugged toggle action that locks "over center" for safety
- No drilling is ever required on your stage floor—just lock these Wagon Brakes in place



Have questions about our products? Contact us!

www.CarrLane.com cs@carrlane.com 314.647.6200

Follow Us!

- f Carr Lane Manufacturing Co.
- in Carr Lane Manufacturing Co.
- @CarrLane
- CarrLaneMfg



Learn More



Stage Products

Carr Lane tooling components including wagon brakes, lifting pins, hoist rings & more are trusted on stages across the globe.



Wagon Brakes



CL-150-SPC-BZ

The medium-size plunger clamp shown here has a 1-1/4" plunger travel, and locks in extended and retracted position. The plunger is tapped to accept any 5/16-18 threaded foot. 300 lbs holding capacity.



CL-250-SPC-BZ

The heavy-duty plunger clamp shown here has a 1-5/8" plunger travel, and locks in extended and retracted position. The plunger is tapped to accept any 3/8-16 threaded foot. 800 lbs holding capacity.



Tapped Plunger

- Low profile plunger clamp
- Locks in extended or retraced position



Lifting Pins

A single-acting ball lock pin with a solid, one-piece body and four balls for high tension loads. Positive locking until released by pushing the button. Sturdy forged shackle for heavy lifting. Manganese phosphate finish provides excellent lubricity and corrosion resistance.

Safety Lifting Devices (Hoist Rings)

The original safety-engineered hoist ring. Swivel hoist ring pivots 180 degrees and swivels 360 degrees simultaneously to allow lifting from any direction. Safety factor = 5:1.



Swivel

Side Pull

Hoist Ring Hoist Ring



Hoist Ring




Lifting



Eye



Precision alignment pin with a ground shank. This popular singleacting type is positive locking until released by pushing the button, which moves the center spindle forward to allow the locking balls to retract into a radial groove. This type has the widest range of types and sizes. Available in steel or stainless steel. Made in USA.





Threaded Inserts

These key-locking threaded inserts are ideal for thread reinforcement, especially when the mating stud or bolt will be removed frequently. Available in inch ID thread sizes from #10-24 to 1-1/2"-12 and metric sizes from M5 to M24. They provide strong, permanent steel threads in a weaker parent material ferrous, non-ferrous, or non-metallic. Key Inserts are also well suited for quick repair of stripped, damaged, or worn threads.