



Green-Light Your Next Project with **Quick Ship Bushings** from Carr Lane Manufacturing



*Now our most popular
Drill Bushing items are
in stock and ready to
ship fast!*

CarrLane
MANUFACTURING CO.

Carr Lane Manufacturing Co. | 314.647.6200 | www.carrlane.com

More Than 300 Styles In Stock And Ready To Ship

H Bushings
H168.0980
H168.1285
H244.2210
H266.2500
H328.3125
H408.3750
H484.5000
H486.5000
H488.5000
H5616.6250
H568.6250
H648.7500

HM Bushings
HM12168.00
HM151210.00
HM182012.00
HM221615.00
HM302020.00
HM302022.00
HM553042.00



L Bushings
L288
L3216
L324
L328
L6412
L6416
L6424
L648
L8812
L8816
L8822

PM Bushings
PM10106.00
PM12106.80
PM12108.00
PM12168.00
PM151210.00
PM15128.40
PM181212.00
PM302020.00
PM422530.00
PM683.00
PM8125.00

P Bushings									
P138.0980	P2016.1910	P208.1440	P266.1865	P288.2500	P3216.3125	P328.2210	P408.3281	P4822.5312	P6412.6562
P164.0980	P204.1250	P208.1470	P266.1910	P288.2510	P3216.3160	P328.2280	P408.3438	P4824.5000	P6412.7500
P164.1250	P204.1285	P208.1495	P266.2188	P288.2656	P326.1875	P328.2500	P408.3740	P4824.6250	P6416.5000
P164.1285	P204.1406	P208.1562	P266.2490	P288.2812	P326.1935	P328.2520	P408.3750	P488.3750	P6416.6250
P166.0980	P204.1570	P208.1590	P266.2500	P3212.1875	P326.1960	P328.2570	P408.3770	P488.4375	P6416.6562
P168.0980	P204.1875	P208.1610	P268.1875	P3212.1960	P326.2010	P328.2610	P408.3906	P488.4531	P6416.6875
P168.0995	P204.1890	P208.1660	P268.1910	P3212.2010	P326.2031	P328.2656	P408.4062	P488.4688	P6416.7500
P168.1065	P204.1910	P208.1719	P268.1935	P3212.2031	P326.2130	P328.2720	P408.4219	P488.4844	P6420.6719
P168.1094	P205.1660	P208.1730	P268.1960	P3212.2188	P326.2188	P328.2770	P408.4375	P488.5000	P6420.6875
P168.1110	P205.1875	P208.1770	P268.2010	P3212.2210	P326.2210	P328.2812	P408.5000	P488.5010	P6420.7500
P168.1130	P205.1935	P208.1800	P268.2188	P3212.2280	P326.2380	P328.3020	P4810.3750	P5610.5000	P6422.6250
P168.1200	P206.1250	P208.1875	P268.2500	P3212.2500	P326.2500	P328.3125	P4810.5000	P5610.5625	P6422.7500
P168.1250	P206.1470	P208.1890	P268.2510	P3212.2570	P326.2570	P328.3160	P4810.5156	P5610.6250	P6424.7500
P168.1285	P206.1495	P208.1910	P268.2570	P3212.2656	P326.2656	P328.3750	P4812.3750	P5612.5000	P648.5000
P168.1360	P206.1520	P208.1935	P2810.2500	P3212.2770	P326.2812	P4012.3750	P4812.4375	P5612.5625	P648.6250
P168.1405	P206.1562	P2612.1875	P2812.2344	P3212.2812	P326.3115	P4012.3770	P4812.4531	P5612.6250	P648.6562
P168.1406	P206.1590	P2612.2500	P2812.2500	P3212.2969	P326.3125	P4012.4375	P4812.4990	P5616.5000	P648.6875
P2010.1495	P206.1610	P2612.2510	P2812.2812	P3212.3020	P326.3160	P4012.5000	P4812.5000	P5616.5938	P648.7500
P2010.1875	P206.1719	P2616.1875	P2816.2500	P3212.3125	P326.3750	P4016.3125	P4812.5312	P5616.6250	
P2012.1250	P206.1730	P2616.2210	P2816.2570	P3212.3160	P328.1875	P4016.3750	P4816.3750	P5620.6250	
P2012.1406	P206.1800	P2616.2500	P284.2500	P3216.1875	P328.1910	P4016.3906	P4816.4219	P5622.6250	
P2012.1562	P206.1875	P264.1875	P284.2812	P3216.2130	P328.1935	P4016.4062	P4816.4375	P5624.6250	
P2012.1590	P206.1890	P264.1910	P285.2500	P3216.2188	P328.1960	P4016.4375	P4816.5000	P568.5625	
P2012.1719	P206.1910	P264.2500	P285.2660	P3216.2500	P328.2010	P4016.5000	P4820.5000	P568.6250	
P2012.1875	P208.1250	P264.2570	P286.2344	P3216.2656	P328.2031	P4022.3125	P4822.3750	P568.6406	
P2012.1910	P208.1285	P265.2500	P286.2500	P3216.2660	P328.2130	P406.3750	P4822.4375	P6412.5000	
P2016.1875	P208.1406	P265.2570	P288.2344	P3216.2812	P328.2188	P408.3125	P4822.5000	P6412.6250	

INCH				METRIC			
P	- 20	- 8	- .1250	PM	- 8	- 12	- 4.50
Type	OD	Length	ID as	Type	OD	Length	ID
	in 64ths	in 16ths	4-place		in	in	as 2-place
	of an inch	of an inch	decimal inch		mm	mm	decimal mm