



Standard jaw smooth/serrated

Part no.	a	b	c
5.2058.1003	100	34	13
5.2058.1004	125	45	15
5.2058.1005	160	54	18




Top step jaw

for fixed jaw Part no.	for slide Part no.	a	c	d	e	h	l	m	p
9.3284.0201	9.3284.1201	100	11,5	6	34	6,5	48	60	10h6
9.3284.0301	9.3284.1301	125	14,0	6	40	9,0	58	65	12h6
9.3284.0401	9.3284.1401	160	17,0	8	43	12,0	64	88	18h6




Precision step jaw

Part no.	a	b	c	d	e	f	g
5.2082.0001	100	34	29	10	19	15	11
5.2082.0002	125	45	39	13	25	20	16
5.2082.0003	160	54	45	15	25	20	16




Pendulum jaw

Part no.	a	b	c	d
8.3711.0208	100	34	35	16
8.3711.0308	125	45	50	22
8.3711.0408	160	54	55	26




Vee jaw

Part no.	a	b	b1	c	d
5.3030.0002	100	34	19	17	8 – 35
5.3030.0003	125	45	27	19	10 – 50
5.3030.0004	160	54	32	21	12 – 60




Clamping jaw, soft

Part no.	a	b	c
5.2055.0097	100	36	20
5.2055.0098	125	47	25
5.2055.0099	160	56	30



Clamping jaw, extra high

Part no.	a	b	c	d	e
9.3283.0201	100	58,0	25	25	60
9.3283.0301	125	75,5	32	32	74
9.3283.0401	160	92,5	40	40	100



Clamping jaw extra large

Part no.	a	b	c	d
5.2058.1025	100	34	13	125
5.2058.1026	125	45	15	160
5.2058.1027	160	54	20	200

all dimensions in mm