


Heavy-Duty Quarter Turn Ball Lock Pin
Installation Data



PART NO.	B DIA (mm)	J THREAD	L DIA (mm)	M DIA (mm)	P THREAD	R DIA (mm)	S (mm)	T DIA (mm)	U DIA (mm)	V DIA (mm)	W (mm)	MAX CLAMP PLATE THICKNESS (mm)	MINIMUM RECEIVER PLATE THICKNESS (mm)
CLM-12-QTBHx	14	M2	21	29	M3	23	4	26	4.4	16.5	6	16	10
CLM-16-QTBHx	18	M3	28	37	M4	29	5	35	6.5	22	8	20	13